MAGNETIC STIRRER

DESCRIPTION

It is mainly used to mix different substances in small laboratories. It adopts electric motor to make magnet whirl, and magnetic force drives mill assistant to mix.

ECOSHIL

TECHNICAL PARAMETERS

MODEL	STIRRER-I
Maximum velocity	2000 rpm
Maximum volume	1000 mL
Plate size	Φ 130 mm
Exterior size	Φ 130 x 60 mm
Weight	Approx. 0.3 kg
Power	10 W
Power supply	110V, 60Hz



Ecoshel reserves all the rights to changes in product design, if there are any design change, we will not inform in advance.

STANDARD ACCESSORIES

- 1. Magnetic stirring bar ~29 mm
- 2. Power adapter
- 3. USB cable

KEY FEATURES

- 1. Lightweight, durable, and small design.
- 2. Made of plastic material (ABS).
- 3. Stirring speed adjustable.



Ecoshel reserves all the rights to changes in product design, if there are any design change, we will not inform in advance.